



BEST VALUE AT THE LOWEST COST



Ideal for Anterior restorations



Ideal for Posterior restorations



\$ FCZ

FULL CONTOUR ZIRCONIA



\$\$ NATZRAL

SUPER TRANSLUCENT ZIRCONIA



\$\$\$ E.MAX

LITHIUM DISILICATE



\$\$\$\$ PFZ

PORCELAIN FUSED ZIRCONIA

TRANSLUCENT

No

Yes

Yes

Translucent porcelain /
opaque substructure

OPAQUE

Yes

No

No

Yes

DISCOLORED
PREP

Yes

≤ 2 Shades darker than
desired shade
(No metal posts)

≤ 2 Shades darker than
desired shade
(No metal posts)

Yes

BRIDGE

Requires ≥ 5mm
occlusal free space

Up to 3 units in
the anterior

Up to 3 units in
the anterior

Requires ≥ 5mm
occlusal free space

IMPLANTS

Yes

Requires a custom zirconia
or titanium abutment

Requires a custom zirconia
or titanium abutment

Yes

MULTIPLE
SHADES

As long as the shade
variation is the same
category and no more
than 2 shade difference

As long as the shade
variation is the same
category and no more
than 2 shade difference

As long as the shade
variation is the same
category and no more
than 2 shade difference

Yes

OCCUSAL
CLEARANCE

1.0mm - 1.5mm

1.5mm - 2.0mm

1.5mm - 2.0mm

1.0mm - 1.5mm

PREP DESIGN

All OK just make sure the
margin is not undercut

Preferably a heavy
Chamfer or soft shoulder
but beveled is OK

Preferably a heavy
Chamfer or soft shoulder
but beveled is OK

Preferably a heavy
Chamfer or soft shoulder
but beveled is OK

STRENGTH

1200 MPA

750 MPA

400 MPA

Substructure = 1200 mpa
Porcelain = 120 mpa

IVERSON ADDS VALUE AND SAVES CHAIR TIME

14437 Meridian Parkway • Riverside CA 92518 • Ph: (800) 334-2057 • www.IversonDental.com